MTi-320

- Small, IP51-rated AHT
- 0.5 deg roll/pitch accuracy
- Full graphical user interface (GUI) and Starter Kit (SK) available

The MTi-320 is a high-performing Active Heading Tracker (AHT) with a small form factor design for deep integration in your application.

The Xsens optimized strapdown algorithm (AttitudeEngine TM) performs high-speed, dead-reckoning calculations at 1 kHz, accurately capturing high-frequency motions. Xsens' industry-leading sensor fusion algorithm provides high accuracy and sensor auto-calibration in this cost-effective module for a wide range of (embedded) applications.

The MTi-320 is supported by the MT Software Suite, which includes MT Manager (GUI for Windows/Linux), SDK, example codes and drivers for many platforms including ROS.



This document is informational and not binding.

Complete and detailed specifications are available at mtidocs.movella.com

- White label and OEM integration options available
- 3D models available on request

Complete and detailed specifications are available at **mtidocs.movella.com**

Sensor Fusion Performance	
Roll, Pitch	0.5 deg RMS
Yaw/Heading ——————	unreferenced, low drift
Strapdown Integration (SDI) ———	Yes
Gyroscope	
Standard full range	2000 deg/s
Bandwidth (-3dB)	230 Hz
Accelerometer	
Standard full range	16 g
Bandwidth (-3dB)	230 Hz
Magnetometer	
Standard full range —————	+/- 8 G
Total RMS noise	0.5 mG
Non-linearity	0.2%
Resolution ——————	0.25 mG

Mechanical

IP-rating	IP51
Operating Temperature ———	-40 to 85 °C
Casing material	PC-ABS
Mounting orientation ————	No restriction, full 360° in all axes
Dimensions —————	28x31.50x13 mm
Connector —	8-pin Molex Micro-Lock 26-30 AWG
Weight ————	9 g
Certifications	CE ECC RoHS

Electrical

Input voltage —		4.5 to 24V
Power consumption	(typ)	300 mW

Interfaces / IO

Interfaces ——————	RS232
Sync Options	Yes
Protocols —	Xbus
Clock drift	10 ppm
Output Frequency	up to 1kHz, 100 Hz SDI
Built-in-self test	Gyr, Acc, Mag

Software Suite

GUI (Windows/Linux)	MT Manager, Firmware updater,
	Magnetic Field Mapper
SDK (Example code)	C++, C#, Python, Matlab, Nucleo,
	public source code
Drivers	LabVIEW, ROS, GO
Support ————	Online manuals, community and
	knowledge base



