

Xsens MTi-620R

- > Rugged, IP 68 rated VRU
- > 0.2 deg roll/pitch accuracy
- > Full GUI and SDK available



Description

The MTi-620R is a Vertical Reference Unit (VRU) with a rugged housing featuring IP68 protection against environmental influences. Building on the proven Xsens MTi 600-series technology it enables a robust and easy to use orientation tracking. It is designed for easy integration and seamless interfacing with other equipment.

The MTi-620R is supported by the MT Software Suite which includes MT Manager (GUI for Windows/Linux), SDK, example codes and drivers for many platforms including ROS.

- > White label and OEM integration options available
- > 3D models available on request

Sensor Fusion Performance

Roll/Pitch	0.2 deg RMS
Yaw/Heading	Unreferenced, low drift
Strapdown Integration (SDI)	Yes

Gyroscope

Standard full range	2000 deg/s
In-run bias stability	8 deg/h
Bandwidth (-3dB)	520 Hz
Noise Density	0.007 °/s/√Hz
g-sensitivity (calibr.)	0.1 °/s/g

Accelerometer

Standard full range	10 g
In-run bias stability	10 (x,y) 15(z) mG
Bandwidth (-3dB)	500 Hz
Noise Density	60 mG/√Hz

Magnetometer

Standard full range	+/- 8 G
Total RMS noise	1 mG
Non-linearity	0.2%
Resolution	0.25 mG

Barometer

Standard full range	300-1250 hPa
Total RMS noise	1.2 Pa
Relative accuracy	+/- 8 Pa (~0.5m)

Mechanical

IP-rating	IP68
Operating Temperature	-40 to 85 °C
Casing material	Aluminum
Mounting orientation	No restriction, full 360° in all axes
Dimensions	56.5x40.9x24.75 mm
Connector	Main: ODU (AMC HD 12 pins)

Weight	75 g
Certifications	CE, FCC, RoHS

Electrical

Input voltage	4.5 to 24V
Power consumption (typ)	<0.5 W

Interfaces / IO

Interfaces	CAN, RS232
Sync Options	SyncIn, SyncOut, ClockSync
Protocols	Xbus, ASCII (NMEA) or CAN
Clock drift	10ppm (or external)
Output Frequency	Up to 2 kHz, 400 Hz SDI
Built-in-self test	Gyr, Acc, Mag, Baro

Software Suite

GUI (Windows/Linux)	MT Manager, Firmware updater, Magnetic Field Mapper
SDK (Example code)	C++, C#, Python, Matlab, Nucleo, public source code
Drivers	LabVIEW, ROS, GO
Support	Online manuals, community and knowledge base